


ND

ΣΕΙΡΑ SERIES



125S	40	135x110	105x80	11	175	55	110		250	H-125S-ND.B-TS	H-125S-ND.B-TF	H-125S-ND.B-TSFP	
										H-125S-ND.R-TS	H-125S-ND.R-TF	H-125S-ND.R-TSFP	
										H-125S-ND.S-TS	H-125S-ND.S-TF	H-125S-ND.S-TSFP	
150S	45	135x110	105x80	11	200	58	110		350	H-150S-ND.B-TS	H-150S-ND.B-TF	H-150S-ND.B-TSFP	
										H-150S-ND.R-TS	H-150S-ND.R-TF	H-150S-ND.R-TSFP	
										H-150S-ND.S-TS	H-150S-ND.S-TF	H-150S-ND.S-TSFP	
175	45	135x110	105x80	11	238	65	110		400	H-175-ND.B-TS	H-175-ND.B-TF	H-175-ND.B-TSFP	
										H-175-ND.R-TS	H-175-ND.R-TF	H-175-ND.R-TSFP	
										H-175-ND.S-TS	H-175-ND.S-TF	H-175-ND.S-TSFP	
200	50	135x110	105x80	11	250	65	110		550	H-200-ND.B-TS	H-200-ND.B-TF	H-200-ND.B-TSFP	
										H-200-ND.R-TS	H-200-ND.R-TF	H-200-ND.R-TSFP	
										H-200-ND.S-TS	H-200-ND.S-TF	H-200-ND.S-TSFP	
250	60	135x110	105x80	11	300	65	110		800	H-250-ND.B-TS	H-250-ND.B-TF	H-250-ND.B-TSFP	
										H-250-ND.R-TS	H-250-ND.R-TF	H-250-ND.R-TSFP	
										H-250-ND.S-TS	H-250-ND.S-TF	H-250-ND.S-TSFP	



080	30	105x85	80x60	9	118	40	95		125	LV-080-ND.S-TS	LV-080-ND.S-TF	LV-080-ND.S-TSFP	
100S	40	105x85	80x60	9	128	40	95		175	LV-100S-ND.R-TS	LV-100S-ND.R-TF	LV-100S-ND.R-TSFP	
									175	LV-100S-ND.S-TS	LV-100S-ND.S-TF	LV-100S-ND.S-TSFP	
125S	40	135x110	105x80	11	178	50	140		250	LV-125S-ND.B-TS	LV-125S-ND.B-TF	LV-125S-ND.B-TSFP	
									250	LV-125S-ND.R-TS	LV-125S-ND.R-TF	LV-125S-ND.R-TSFP	
									250	LV-125S-ND.S-TS	LV-125S-ND.S-TF	LV-125S-ND.S-TSFP	
150S	45	135x110	105x80	11	210	53	140		350	LV-150S-ND.B-TS	LV-150S-ND.B-TF	LV-150S-ND.B-TSFP	
									350	LV-150S-ND.R-TS	LV-150S-ND.R-TF	LV-150S-ND.R-TSFP	
									350	LV-150S-ND.S-TS	LV-150S-ND.S-TF	LV-150S-ND.S-TSFP	
175	45	135x110	105x80	11	223	53	140		400	LV-175-ND.B-TS	LV-175-ND.B-TF	LV-175-ND.B-TSFP	
									400	LV-175-ND.R-TS	LV-175-ND.R-TF	LV-175-ND.R-TSFP	
									400	LV-175-ND.S-TS	LV-175-ND.S-TF	LV-175-ND.S-TSFP	
200	50	135x110	105x80	11	245	65	140		550	LV-200-ND.B-TS	LV-200-ND.B-TF	LV-200-ND.B-TSFP	
									550	LV-200-ND.R-TS	LV-200-ND.R-TF	LV-200-ND.R-TSFP	
									550	LV-200-ND.S-TS	LV-200-ND.S-TF	LV-200-ND.S-TSFP	
250	60	135x110	105x80	11	297	67	140		800	LV-250-ND.B-TS	LV-250-ND.B-TF	LV-250-ND.B-TSFP	
									800	LV-250-ND.S-TS	LV-250-ND.S-TF	LV-250-ND.S-TSFP	

ΒΙΟΜΗΧΑΝΙΚΕΣ ΕΦΑΡΜΟΓΕΣ

3.6

